




AMP

TE Internal #: 205975-1

Rack & Panel Covers & Plugs, Sealing Plug, Hermaphroditic, Silicone Rubber, Cable-to-Panel, Sealable, Wire & Cable, Cable Mount (Free-Hanging)

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Backplane > Rack & Panel Covers & Plugs



Protection & Strain Relief Accessory Type: **Sealing Plug**

Compatible With Connector Style: **Hermaphroditic**

Primary Product Material: **Silicone Rubber**

Connector System: **Cable-to-Panel**

Sealable: **Yes**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Sealing Plug
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Body Features

Primary Product Color	Red
Primary Product Material	Silicone Rubber

Contact Features

Compatible With Contact Size	5
------------------------------	---

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Usage Conditions

Compatible With Connector Style	Hermaphroditic
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Packaging Features

Packaging Method	Package
------------------	---------

Other

--	--



Comment

For A404 and A600

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JAN 2019 (197)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

Product Drawings

[SEALING PLUG,COAX,ARINC](#)

English

CAD Files

Customer View Model

[ENG_CVM_205975-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_205975-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_205975-1_A.2d_dxf.zip](#)



English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ARINC 600 Next Generation Receptacle Connector](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMP RM AND RME SERIES CONNECTORS WITH SIZE 5 AND 9 COAXIAL CONTACTS](#)

English