



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Boots & Strain Relief



Protection & Strain Relief Accessory Type: **Cable Grip**
Compatible With Circular Connector Shell Size: **17**

Features

Product Type Features

Product Type	Accessory
Accessory Color	Black
Protection & Strain Relief Accessory Type	Cable Grip

Body Features

Cable Grip Color	Black
Cable Grip Material	Thermoplastic
Color	Black
Cable Grip Range	5.08 – 6.35 mm[.2 – .25 in]
Cable Clamp Color	Black

Operation/Application

Compatible With Circular Connector Shell Size	17
---	----

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>











Compatible Parts

 TE Part # CAT-AM71-C83998J Cable/Panel Mount Connector, CPC Series 1	 TE Part # CAT-AM71-C83998M CPC Connectors, Series 2	 TE Part # CAT-AM71-C83998BB CPC SERIES 3	 TE Part # CAT-AM71-C83998F Connectors with Posted Pin Contacts, CPC Series 1
 TE Part # CAT-AM71-C83998DD Connectors, CPC Series 2, with Posted Contacts	 TE Part # 205839-3 CPC PLUG ASSEMBLY SIZE 17-28	 TE Part # 1-207369-3 CPC RECEPT ASSY SZ 17-28 LF	 TE Part # 1-207369-1 CPC RECEPT ASSY SIZE 17-28 LF



Also in the Series

AMP CPC



Documents

Product Drawings

CABLE GRIP,SZ 17,CPC

English

CAD Files

3D PDF

English

Customer View Model



[ENG_CVM_207387-1_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_207387-1_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_207387-1_H.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_207387-1_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207387-1_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207387-1_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[MD_207387-1_04092014019_dmtec](#)

English

[MD_207387-1_04092014019_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English