



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers > CPC SEALED ACCESSORIES



Protection & Strain Relief Accessory Type: **Sealing Cap**
 Compatible With Circular Connector Shell Size: **23**
 Cap to Flange Attachment: **Plastic Strap**
 Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

[All CPC SEALED ACCESSORIES \(2\)](#)

Features

Product Type Features

Product Type	Accessory
Protection & Strain Relief Accessory Type	Sealing Cap

Body Features

Sealing Cap Material	Thermoplastic
Color	Black
Cap Material	Thermoplastic

Mechanical Attachment

Cap to Flange Attachment	Plastic Strap
--------------------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Compatible With Circular Connector Shell Size	23
---	----

Packaging Features

--	--



Packaging Quantity	100
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-C83998Y
One-Piece Connector, Sealed, CPC Series 1



TE Part # CAT-AM71-C83998J
Cable/Panel Mount Connector, CPC Series 1













TE Part # CAT-AM71-C83998BB
CPC SERIES 3



TE Part # CAT-AM71-C83998K
Circular Connector, Environmentally Sealed, CPC Series 6



Also in the Series | AMP CPC



Documents

Product Drawings

[SEALING CAP ASSY,SZ 23,CPC](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_207446-3_P.2d_dxf.zip](#)

English



[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_207446-3_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207446-3_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

CSA Certificate

English