

AMP


TE Internal #: 205103-3

Rack & Panel Contacts, Socket, 22 Shell Size, Standard, Length

16.26 mm [.64 in], Gold, Wire & Cable

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Backplane > Rack & Panel Contacts

Contact Type: **Socket**Rack & Panel Connector Contact Size: **22**Rack & Panel Connector Contact Style: **Standard**Contact Length: **16.26 mm [.64 in]**Contact Mating Area Plating Material: **Gold****Features****Product Type Features**

Connector & Contact Terminates To	Wire & Cable
-----------------------------------	--------------

Body Features

Contact Removal Style	Rear Release
-----------------------	--------------

Contact Features

Contact Orientation	Straight
Contact Base Material	Copper Alloy
Contact Type	Socket
Rack & Panel Connector Contact Size	22
Rack & Panel Connector Contact Style	Standard
Contact Length	16.26 mm [.64 in]
Contact Mating Area Plating Material	Gold

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Retention Clip
---------------------------------------	----------------

Dimensions

Wire Size	.12 – .4 mm ²
-----------	--------------------------

Identification Marking



Contact Color Code	Brown/Yellow/Gray
--------------------	-------------------

Packaging Features

Packaging Method	Tape
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2022 (224)</p> <p>Candidate List Declared Against: JAN 2022 (223)</p> <p>SVHC > Threshold:</p> <p>Pb (1% in Component Part)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

SKT CONTACT, SZ 22

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_205103-3_AN.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205103-3_AN.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205103-3_AN.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ARINC 600 Next Generation Receptacle Connector

English

Instruction Sheets

Instruction Sheet (U.S.)

English

ARINC 404 RACK-AND-PANEL CONNECTORS SERIES R, RM, RME, M, MM, MME

English

Instruction Sheet (U.S.)

English