

208211-1 ✓ ACTIVE

AMP | AMP Metrimate

TE Internal #: 208211-1

Rectangular Connector Hardware, Mounting Screw, Wire-to-Panel,  
Wire & Cable, Power & Signal, Panel Mount, -55 – 130 °C [-67 – 266  
°F], AMP Metrimate

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Mounting Screw**

Connector System: **Wire-to-Panel**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Circuit Application: **Power & Signal**

## Features

### Product Type Features

Product Type	Accessory
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Body Features

Material	Stainless Steel
----------	-----------------

### Mechanical Attachment

Screw & Hole Thread Size	M4 x 0.7-6G
Hardware Type	Mounting Screw
Connector Mounting Type	Panel Mount

### Dimensions

Height	5.08 mm[.2 in]
Length	21.33 mm[.84 in]



### Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

### Operation/Application

For Use With	Plug Housing
Circuit Application	Power & Signal

### Packaging Features

Packaging Quantity	1
Packaging Method	Package

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability









#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Also in the Series | AMP Metrimate



## Documents

### Product Drawings

[SCREW SHOULDER, SPEC](#)

English

### CAD Files

[Customer View Model](#)

[ENG\\_CVM\\_208211-1\\_M.3d\\_igs.zip](#)

English



**Customer View Model**

[ENG\\_CVM\\_208211-1\\_M.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_208211-1\\_M.2d\\_dxf.zip](#)

English

**3D PDF**

English

**3D PDF**

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_208211-1\\_S.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_208211-1\\_S.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_208211-1\\_S.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

[METRIMATE\\_PIN\\_SOCKET\\_CATALOG](#)

English

---

**Product Specifications**

[Application Specification](#)

English