

207654-1 ✓ ACTIVE

METRIMATE

TE Internal #: 207654-1

Rectangular Connector Keying Plugs, Keying Plug, 1 Position, -67 – 266 °F [-55 – 130 °C]

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Keying Plugs



Connector Keying Accessory Type: **Keying Plug**

Number of Positions: 1

Operating Temperature Range: -55 – 130 °C [-67 – 266 °F]

Features

Product Type Features

Product Type	Accessory
Connector Keying Accessory Type	Keying Plug

Configuration Features

Number of Positions	1
---------------------	---

Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	Plug Housing
--------------	--------------

Industry Standards

UL Flammability Rating	UL 94V-0
VDE Tested	Yes
Agency/Standard	CSA, UL

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Comment	To be used in socket cavities of connector plug only.
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents



Product Drawings

KEYING PLUG

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_207654-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207654-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_207654-1_F.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_207654-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_207654-1_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_207654-1_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

METRIMATE Self-Locking Connectors

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English