

213426-1 ✓ ACTIVE

AMP | AMP Metrimate

TE Internal #: 213426-1

Rectangular Connector Housings, Wire-to-Panel / Wire-to-Board / Wire-to-Wire, 15 Position, .2 in [5.08 mm] Centerline, 5 Row, AMP Metrimate

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Housings



Connector System: **Wire-to-Board, Wire-to-Panel, Wire-to-Wire**

Number of Positions: **15**

Centerline (Pitch): **5.08 mm [.2 in]**

Row-to-Row Spacing: **4.39 mm [.173 in]**

Number of Rows: **5**

Features

Product Type Features

Connector System	Wire-to-Board, Wire-to-Panel, Wire-to-Wire
Connector & Housing Type	Plug
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable
Connector Type	Housing
Product Type	Connector
Wire/Cable Type	Discrete Wire
Wire Type	Stranded

Configuration Features

Number of Positions	15
Number of Rows	5

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Contact Type	Socket
Contact Current Rating (Max)	55 A

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	5.08 mm[.2 in]
Housing Material	Polyester GF
Housing Color	Black

Dimensions

Row-to-Row Spacing	4.39 mm[.173 in] 2.162 in
Panel Thickness	.031 – .091 in, .8 – 2.3 mm

Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
For Use With	Receptacle Housing

Industry Standards

Agency/Standard	CSA, UL, VDE
VDE Tested	Yes
UL File Number	E28476
UL Flammability Rating	UL 94V-0
UL Rating	Certified, Recognized

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP Metrimate





Rectangular Connector Housings(35)



Rectangular Connector Keying Plugs(1)



Rectangular Contact Inserts(4)



Rectangular Power Connectors(2)



Standard Rectangular Connectors(5)

Documents

Product Drawings

PLG HSG,3 POWR,12 SGNL,METRI

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_213426-1_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213426-1_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213426-1_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_213426-1_E1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_213426-1_E1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_213426-1_E1.2d_dxf.zip](#)

English

[3D PDF](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Power Contacts

English

METRIMATE_PIN_SOCKET_CATALOG

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English