



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Dust Cap**

Cap to Flange Attachment: **Push/Pull**

Number of Positions: **1**

Sealable: **No**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Features

Product Type Features

Connector Design	Circular
Product Type	Accessory
Connector Style	Receptacle
Protection & Strain Relief Accessory Type	Dust Cap
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Sealing Cap Plating Material	Black Chromate
Shell Finish	Black Chromate
Cap Material	Brass

Mechanical Attachment

Cap to Flange Attachment	Push/Pull
Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Panel Thickness	5 mm[.197 in]
-----------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------



Operation/Application

For Use With	Receptacle Connector
--------------	----------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Other

Comment	1
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with tin/lead solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

Product Drawings

[DUST CAP,RCPT,Sz105,F SERIES](#)

English



Datasheets & Catalog Pages

Products for Aerospace and Defense

English

Product Specifications

Product Specification

English