




Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Protective Cap**

Compatible With Circular Connector Shell Size: **14**

Cap to Flange Attachment: **Metal Bead Chain**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Product Type	Accessory
Protection & Strain Relief Accessory Type	Protective Cap

Body Features

Sealing Cap Plating Material	Nickel
Sealing Cap Material	Zinc Alloy
Cap Material	Zinc
Sealing Gasket Material	Elastomer

Mechanical Attachment

Bead Chain Material	Nickel
Bead Chain Coupling Material	Nickel
Bead Chain Coupling Plating Material	Brass
Bead Chain Plating Material	Steel
Cap to Flange Attachment	Metal Bead Chain

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	Receptacle
Compatible With Circular Connector Shell Size	14

Packaging Features

Packaging Quantity	10
Packaging Method	Carton

Other

Comment	For Metal-Shell CPC Receptacles Only.
---------	---------------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)




Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Connector Seals(36)



Circular Power Connectors(467)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Documents

Product Drawings

CMC DUST CAP ASSM,SIZE 14

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_213823-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_213823-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_213823-2_B.3d_stp.zip](#)

English



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_213823-2_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213823-2_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213823-2_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English

Product Specifications

[Application Specification](#)

English