

**AMPLIMITE**

TE Internal #: 211011-1

TE Internal Description: AMPLIMITE CONN SVR,26 POS,TRW

[View on TE.com >](#)

Connectors &gt; D-Shaped Connectors &gt; D-Sub Accessories &gt; D-Sub Connector Savers

Connector & Housing Type: **Plug, Receptacle**Number of Positions: **26**Compatible With Connector Shell Size: **2**D-Sub Contact Size: **22**Non-Magnetic: **Yes****Features****Product Type Features**

Product Type	Connector
Connector & Housing Type	Plug, Receptacle

**Configuration Features**

Number of Positions	26
---------------------	----

**Body Features**

Shell Plating Material	Cadmium
Shell Material	Steel
Non-Magnetic	Yes

**Contact Features**

Contact Mating Area Plating Material	Gold
Contact Base Material	Beryllium Copper
D-Sub Contact Size	22

**Operation/Application**

Compatible With Connector Shell Size	2
--------------------------------------	---

**Industry Standards**

NASA Qualification	No
--------------------	----

**Product Compliance**For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: DEC 2014 (161) SVHC > Threshold: Cd (1.6%) <b>Article Safe Usage Statements:</b> Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Documents

### Product Drawings

[AMPLIMITE CONN SVR,26 POS,TRW](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_211011-1\\_AL.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_211011-1\\_AL.3d\\_igs.zip](#)

English

Customer View Model



[ENG\\_CVM\\_CVM\\_211011-1\\_AL.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Agency Approvals](#)

[UL Report](#)

English