

213900-1 ✓ ACTIVE

AMP | AMP CPC

TE Internal #: 213900-1

Circular Connector Seals, Wire Entry Seal Kit, 10 Position, 15/16-20,
-67 – 221 °F [-55 – 105 °C], AMP CPC

[View on TE.com >](#)



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Seals



Connector Seal Type: **Wire Entry Seal Kit**

Number of Positions: **10**

Screw & Hole Thread Size: **15/16-20**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Seal Type	Wire Entry Seal Kit
---------------------	---------------------

Configuration Features

Number of Positions	10
---------------------	----

Mechanical Attachment

Screw & Hole Thread Size	15/16-20
--------------------------	----------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Individual

Other

Comment	Kit includes (1) Silicon Wire Entry Seal and (1) Pressure Plate., Requires Cable Clamp Kit p/n 213902-1.
---------	--



Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer









This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-AM71-A17 POWERBAND Contacts</p>	 <p>TE Part # CAT-AM71-C83998U Environmentally Sealed Circular Connector, CPC Series 5</p>	 <p>TE Part # 207299-3 FLANGE PLUG MOUNT CPC</p>	 <p>TE Part # CAT-AM71-C83998 CPC Heat Shrink Strain Reliefs</p>
 <p>TE Part # CAT-AM71-C83998W CPC SERIES 5 SEALED ACCESSORIES</p>	 <p>TE Part # CAT-AM71-C83998K Circular Connector, Environmentally Sealed, CPC Series 6</p>	 <p>TE Part # 81665-2 FLANGE GASKET CPC</p>	 <p>TE Part # 213906-1 CPC PLUG ASSY,SRS 6,SZ 17-10</p>



Also in the Series | AMP CPC



Documents



Product Drawings

CPC SEAL ASSY KIT,SRS 6,17-10

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_213900-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_213900-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_213900-1_C.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_213900-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213900-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213900-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English