



AMP

TE Internal #: 2157468-1

Standard Circular Connectors, Wire-to-Panel, 4 Position, Black Chromium, PEEK, 3.31 mm² Wire Size, Size 4, Contacts Preloaded

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Panel**

Number of Positions: **4**

Reverse Gender: **No**

Shell Plating Material: **Black Chromium**

Circular Connector Insulation Material Type: **PEEK**

Features

Product Type Features

Product Type	Connector
Connector System	Wire-to-Panel
Circular Connector Type	Receptacle

Configuration Features

Keying	Single Key
Number of Positions	4
Contacts Preloaded	Yes

Body Features

Shell Plating Material	Black Chromium
Circular Connector Insulation Material Type	PEEK

Contact Features

Reverse Gender	No
Circular Connector Contact Type	Pin

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Polarization

Housing Features

Circular Connector Shell Size	4
-------------------------------	---



Dimensions

Panel Thickness	4.06 mm[.16 in] 1.082 in
Wire Size	3.31 mm ²

Usage Conditions

Operating Temperature Range	-55 – 125 °C
-----------------------------	--------------

Packaging Features

Packaging Quantity	10
--------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2017 (174) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with tin/lead solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

Product Drawings

[PANEL MT RCPT,CIRCULAR HD,4 POS,S/C PINS](#)



English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2157468-1_GN_c-2157468-1-gn.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2157468-1_GN_c-2157468-1-gn.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2157468-1_GN_c-2157468-1-gn.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Aerospace and Defense](#)

English

Product Specifications

[Product Specification](#)

English