

**DDR4 DIMM**

TE Internal #: 2199155-2

DIMM Sockets, Double Data Rate (DDR) 4, Board-to-Bus Bar, 288
Position, Surface Mount Mount, Vertical Module Orientation, DDR4
DIMM

[View on TE.com >](#)

Connectors > Socket Connectors > Memory Sockets > DIMM Sockets > DDR4 DIMM SOCKETS

DRAM Type: **Double Data Rate (DDR) 4**Connector System: **Board-to-Bus Bar**Number of Positions: **288**PCB Mounting Style: **Surface Mount**Module Orientation: **Vertical**[All DDR4 DIMM SOCKETS \(69\)](#)**Features****Product Type Features**

DRAM Type	Double Data Rate (DDR) 4
Connector System	Board-to-Bus Bar
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	288
Module Orientation	Vertical

Body Features

Ejector Type	Standard
--------------	----------

Contact Features

Contact Current Rating (Max)	.75 A
------------------------------	-------

Mechanical Attachment

PCB Mounting Style	Surface Mount
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	.85 mm[.033 in]
--------------------	-----------------



Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Hard Tray
------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | DDR4 DIMM



Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_2199155-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2199155-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2199155-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DDR4 DIMM Socket Flyer \(English\)](#)

English

[DDR4 DIMM Socket Flyer \(Chinese\)](#)

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)



English