

2204406-6 ✓ ACTIVE

MULTI-BEAM | MULTI-BEAM HD


TE Internal #: 2204406-6

Rectangular Power Connectors, Header, Receptacle, Board-to-Board, 24 Position, Printed Circuit Board, UL 94V-0, MULTI-BEAM HD

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Receptacle**

Connector System: **Board-to-Board**

Number of Positions: **24**

Sealable: **No**

Features

Product Type Features

Rectangular Power Connector Type	Header
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions by Circuit Application	4VP/Power, 20/Signal
Number of Positions	24
PCB Mount Orientation	Right Angle
Number of Power Positions	6
Number of Signal Positions	20
Number of Rows	5

Contact Features

PCB Contact Termination Area Plating Material Finish	Matte
------------------------------------------------------	-------



Contact Underplating Material	Palladium Nickel
-------------------------------	------------------

Contact Retention Within Housing	With
----------------------------------	------

Contact Type	Receptacle
--------------	------------

PCB Contact Termination Area Plating Material	Tin
-----------------------------------------------	-----

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Termination Features

Termination Post & Tail Length	3.2 mm
--------------------------------	--------

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
---------------------------------------------	--------------------------

Housing Features

Housing Color	Black
---------------	-------

Housing Material	LCP GF30 (Liquid Crystal Polymer)
------------------	-----------------------------------

Dimensions

Row-to-Row Spacing	2 mm [.079 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C
-----------------------------	--------------

Operation/Application

Circuit Application	Power, Signal
---------------------	---------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Glow Wire Rating	High Temperature Part - Not Glow Wire
------------------	---------------------------------------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
----------------------------------------	---------------------------------------------------------------------------------------------------------------------------------

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | MULTI-BEAM HD



Documents

Product Drawings

MULTI-BEAM HD R/A REC. 4VP+20S

English

MULTI-BEAM HD R/A REC. 4VP+20S

English



CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2204406-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2204406-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2204406-6_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL

English