

216926-1 ✓ ACTIVE

FASTON | FASTON 250

TE Internal #: 216926-1


PCB Terminals, Receptacle, Mating Tab Width .25 in [6.35 mm],

Through Hole - Press-Fit, Tin Plating, Box, FASTON 250

[View on TE.com >](#)



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Receptacle**

PCB Thickness (Recommended): 1.57 mm [.062 in]

Mating Tab Width: 6.35 mm [.25 in]

Mating Tab Thickness: .81 mm [.032 in]

Profile Height from PCB: 13 mm [.518 in]

Features

Configuration Features

Stud Hole	No
Terminal Angle	180 °

Contact Features

PCB Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
Product Terminates To	Printed Circuit Board

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Extension Below Board	5.5 mm[.216 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Profile Height from PCB	13 mm[.518 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 140814-2
250 FASTON,TAB,TPBR



TE Part # 216843-1
250 FASTON,TAB,PCB,TPPB



TE Part # 141878-2
250 FASTON,TAB,TPBR



TE Part # 726386-2
250 FASTON TAB TPBR



TE Part # 725964-2
250 FASTON TAB TPBR



TE Part # 216905-1
POSITIVE LOCK POWER
RECEPTACLE TPPHBRZ



TE Part # 1-726386-2
250 FASTON,TAB,TPBR



TE Part # 140734-2
250 FASTON,TAB,TPBR



TE Part # 140596
250 FASTON,TAB,TPBR



TE Part # 140734-1
250 FASTON,TAB,BR

Also in the Series | **FASTON 250**



Compression Connectors(4)



Crimp Terminal Housings(143)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(144)



Quick Disconnects(455)



Splices(4)

Documents



Product Drawings

POSITIVE LOCK 250 TAB PHBRZ

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_216926-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_216926-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_216926-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Product Specification

English