




TE Internal #: 2169859-1
 Backplane Power Connectors, PCB Mount Receptacle, Board-to-Board, 4 Position, Vertical, Orthogonal, .205 in [5.2 mm] Centerline, Printed Circuit Board

[View on TE.com >](#)

Connectors > Power Connectors > Backplane Power > Backplane Power Connectors



PCB Connector Assembly Type: **PCB Mount Receptacle**

Connector System: **Board-to-Board**

Number of Positions: **4**

PCB Mount Orientation: **Vertical**

Backplane Architecture: **Orthogonal**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Columns	2
Number of Positions	4
PCB Mount Orientation	Vertical
Backplane Architecture	Orthogonal
Stackable	No

Electrical Characteristics

Operating Voltage	48 VDC
-------------------	--------

Contact Features

Contact Current Rating (Max)	25 A
------------------------------	------

Termination Features



Termination Post & Tail Length	2.5 mm[.098 in]
Termination Method to Printed Circuit Board	Through Hole - Press-Fit

Mechanical Attachment

Guide Hardware	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	5.2 mm[.205 in]
Housing Color	Black
Housing Material	LCP (Liquid Crystal Polymer)
UL Flammability Rating	UL 94V-0

Dimensions

PCB Hole Diameter	.73 mm[.029 in]
PCB Thickness (Recommended)	1.6 mm[.062 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

IMP,Power,5PR,VR,Tin

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2169859-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2169859-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2169859-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

2169859-1

Backplane Power Connectors, PCB Mount Receptacle, Board-to-Board, 4 Position,
Vertical, Orthogonal, .205 in [5.2 mm] Centerline, Printed Circuit Board



English