

2170703-6 ✓ ACTIVE

zQSFP+/QSFP28

TE Internal #: 2170703-6

QSFP, QSFP+ & zQSFP+, Cage, 1 x 1, Internal/External EMI Springs, Standard, Data Rate (Max) 28 Gb/s, 1 Port, zQSFP+/QSFP28

[View on TE.com >](#)



Connectors > Pluggable IO Connectors & Cages > QSFP, QSFP+ & zQSFP+



Pluggable I/O Product Type: **Cage**

Port Matrix Configuration: **1 x 1**

EMI Containment Feature Type: **Internal/External EMI Springs**

Included Lightpipe: **No**

Enhancements: **Standard**

Features

Product Type Features

Form Factor	QSFP28/56
Cage Type	Single
Pluggable I/O Product Type	Cage
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Matrix Configuration	1 x 1
Number of Ports	1
Number of Rear EONs per Port Column	1

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Termination Features

Termination Post & Tail Length	2.05 mm[.081 in]
Termination Method to Printed Circuit Board	Through Hole - Press-Fit



Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Heat Sink Compatible	Yes
For Use With Pluggable I/O Products	QSFP28 Cable Assembly, QSFP28 MSA Compatible Transceiver
Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

EMI Containment Feature Type	Internal/External EMI Springs
Included Lightpipe	No
Enhancements	Standard

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C11-Z8
QSFP28 to QSFP28 Cable Assembly:
26 AWG

TE Part # CAT-C11-Z806726
QSFP28 to QSFP28 Cable Assembly:
30 AWG

TE Part # CAT-C11-N49
QSFP28-Two QSFP28 Cable
Assembly: 30 AWG

TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly:
30 AWG

TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly:
26 AWG

TE Part # CAT-Q17-N490325
QSFP56 to QSFP56 Cable Assembly:
30 AWG

TE Part # CAT-Q17-N49033
QSFP56-Two QSFP56 Cable
Assembly: 30 AWG

TE Part # CAT-C11-Q17
QSFP56 to QSFP56 Cable Assembly:
26 AWG

TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG

TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly:
26 AWG


TE Part # 1551920-2
zQSFP+ connector assembly

TE Part # 1888810-2
EMI/Dust Cover, XFP And QSFP

Also in the Series | zQSFP+/QSFP28



Pluggable I/O Cable Assemblies(81)



QSFP, QSFP+ & zQSFP+(432)

Documents

Product Drawings

[CAGE ASSEMBLY, QSFP28 1X1, SPRING](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2170703-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2170703-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2170703-6_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[QSFP28/56 and zQSFP+ Interconnects](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_2170703-6_020620181115_dmtec](#)

English

[MD_2170703-6_020620181115_dmtec](#)

English