

2213142-3 ✓ ACTIVE



NECTOR

TE Internal #: 2213142-3

Plug & Socket Lighting Connectors, Wire-to-Wire, 4 Position, .141 in [3.6 mm] Centerline, Wire & Cable, Bridge, Contacts Preloaded, 125 VAC, 42 VDC

[View on TE.com >](#)

Connectors > Lighting Connectors > Plug & Socket Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **4**

Centerline (Pitch): **3.6 mm [.141 in]**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Product Type	Connector
Accessory Type	Bridge Connector
Wire/Cable Type	Discrete Wire
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Lighting Connector Style	Bridge

Configuration Features

Keying Arrangement	HV-3, HV-4
Number of Positions	4
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	42 VDC
-------------------	--------

Contact Features



Contact Type	Socket
Contact Current Rating (Max)	6 A

Mechanical Attachment

Mounting Angle	Straight
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Color	White
Centerline (Pitch)	3.6 mm [.141 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Documents

Product Drawings

Male to Male Bridge Connector

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2213142-3_A_c-2213142-3-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213142-3_A_c-2213142-3-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213142-3_A_c-2213142-3-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English