



TE Internal #: 2227317-1  
 SFP, SFP+ & zSFP+, Cage, Data Rate (Max) 4 Gb/s, External Springs, SFP, Not Optional, 1 x 1, Through Hole - Press-Fit, 1 Port, Cable-to-Board

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP, SFP+ & zSFP+



Pluggable I/O Product Type: **Cage**

Data Rate (Max): **4 Gb/s**

EMI Containment Feature Type: **External Springs**

Pluggable I/O Applications: **SFP**

Lightpipe Options: **Not Optional**

## Features

### Product Type Features

Form Factor	SFP
Cage Type	Single
Pluggable I/O Product Type	Cage
Lightpipe Options	Not Optional
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Port Matrix Configuration	1 x 1
Number of Ports	1

### Electrical Characteristics

Data Rate (Max)	4 Gb/s
-----------------	--------

### Termination Features

Termination Post & Tail Length	3 mm[.118 in]
--------------------------------	---------------



Termination Method to Printed Circuit Board

Through Hole - Press-Fit

### Mechanical Attachment

Connector Mounting Type

Board Mount

### Housing Features

Cage Material

Stainless Steel

### Dimensions

PCB Thickness (Recommended)

1.5 mm[.059 in]

### Usage Conditions

Operating Temperature Range

-55 – 85 °C[-67 – 185 °F]

### Operation/Application

Heat Sink Compatible

No

For Use With Pluggable I/O Products

SFP Lightpipes

Pluggable I/O Applications

SFP

### Packaging Features

Packaging Method

Box, Box &amp; Tray

### Other

EMI Containment Feature Type

External Springs

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)  
 Candidate List Declared Against: JUNE 2022 (224)  
 Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-SF59-C76264  
SFP Connectors



TE Part # 1367147-1  
SFP COVER, UNPLATED



TE Part # 1367147-3  
SFP COVER, UNPL, NO LOGO



TE Part # 2215077-3  
ASSY, SEATING TOOL, SFP

## Documents

### Product Drawings

[press fit cage assy, single with lp](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2227317-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2227317-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2227317-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Application Specification](#)

English