

RT-3-NO.2-0-COIL ✓ ACTIVE

RAYCHEM | RAYCHEM RT-3


TE Internal #: 278414-000

Heat Shrink Tubing, Black, Single Wall, .32 in [8.13 mm] Expanded Inside, .125 in [3.18 mm] Recovered Inside, 2.5:1 Shrink Ratio, RAYCHEM RT-3

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **8.13 mm [.32 in]**

Recovered Inside Diameter (Max): **3.18 mm [.125 in]**

Shrink Ratio: **2.5:1**

Features

Product Type Features

Product Family	RT-3
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, Water
Primary Product Color	Black
Shrink Ratio	2.5:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Rigid

Dimensions

Recovered Wall Thickness (Tolerance)	.79 mm[.031 in]
Expanded Inside Diameter (Min)	8.13 mm[.32 in]
Recovered Inside Diameter (Max)	3.18 mm[.125 in]

Usage Conditions

Shrink Temperature (Min)	110 °C
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-55 – 135 °C



Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-------------------------------	--

Recovery Temperature	135 °C
----------------------	--------

Product Availability

Applicable Region	Americas, Asia
-------------------	----------------

Packaging Features

Packaging Method	Coil
------------------	------

Other

Meets Low Outgassing Requirements	No
-----------------------------------	----

Product Source	US
----------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
--	--

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM RT-3



Heat Shrink Tubing(25)

Documents

Product Drawings

[RT-3-NO.2-0-COIL](#)

English

Datasheets & Catalog Pages

[RT-3 Pages from 9-1773447-9](#)

English

[Semirigid, Flame-Retardant Polyolefin Heat-Shrinkable Tubing](#)

English

Product Specifications

[Quality Specification](#)

English