



TE Internal #: 2825211-1
 Power Contacts, Contact, 600 VAC, Tin, 22 – 18 AWG Wire Size, .33 – .82 mm² Wire Size, Wire-to-Wire, Wire & Cable, Crimp, Power, Socket

[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
 Operating Voltage: **600 VAC**
 Contact Mating Area Plating Material: **Tin**
 Wire Size: **.33 – .82 mm²**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	13 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Square Post Dimension	1.14 mm[.045 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	2.54 μm[100 μin]
Wire Contact Termination Area Plating Thickness	2.54 μm[100 μin]
Wire Contact Termination Area Plating Material	Pre-Tin



Wire Contact Termination Area Plating Material Finish	Matte
---	-------

Contact Orientation	Straight
---------------------	----------

Contact Underplating Material	Nickel
-------------------------------	--------

Contact Underplating Material Thickness	.762 μm[30 μin]
---	-----------------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.33 – .82 mm ²
-----------	---------------------------

Accepts Wire Insulation Diameter Range	1.5 – 3.1 mm[.06 – .122 in]
--	-----------------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2825208-1
VAL-U-LOK PIN 16AWG HCS SN LP



TE Part # 2825209-1
VAL-U-LOK SKT 16AWG HCS SN LP



TE Part # 2825212-1
VAL-U-LOK PIN HCS TN 22-18 LP



TE Part # 2825213-1
VAL-U-LOK SKT HCS SN 22-18 LP



TE Part # 2151096-1
OCEAN-2.0-APPLICATOR-S-062F125F



TE Part # 2-2151096-1
OCEAN-2.0-APPLICATOR-S-062F125F



TE Part # 2151096-2
OCEAN-2.0-APPLICATOR-S-062F125FA



TE Part # 5-2151096-1
OCEAN-2.0-APPLICATOR-S-062F125F




TE Part # 5-2151096-2
OCEAN-2.0-APPLICATOR-S-062F125FA



TE Part # 7-2151096-1
OCEAN-2.0-APPLICATOR-S-062F125F



TE Part # 7-2151096-2
OCEAN-2.0-APPLICATOR-S-062F125FA



KIT
REPRESENTATION ONLY
TE Part # 7-2151096-7
OCEAN_2.0_SPARE_PART_KIT-062F125F

Documents

Product Drawings

VAL-U-LOK SKT HCS SN 18-22AWG

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_2825211-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2825211-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2825211-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.