

27E895 ✓ ACTIVE

Potter & Brumfield | Potter & Brumfield K10


TE Internal #: 2-1419106-7

Relay Accessories, Sockets & Clips, Socket, DIN Rail Mount, Glass-Filled Polyester, K10 Relays, DIN Rail Snap Mount, 2, Socket, Potter & Brumfield K10

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Relay Accessories, Sockets & Clips



Relay Accessory, Socket & Clip Product Type: **Socket**

Relay Accessory, Socket & Clip Socket Type: **DIN Rail Mount**

Grounding Provision: **Without**

Relay Accessory, Socket & Clip Body Material: **Glass-Filled Polyester**

Relay Accessory, Socket & Clip For Use With: **K10 Relays**

Features

Product Type Features

Terminal Configuration	Screw, DIN Rail Snap-Mount
Relay Accessory, Socket & Clip Product Type	Socket
Relay Accessory Type	Socket

Configuration Features

Grounding Provision	Without
---------------------	---------

Body Features

Relay Accessory, Socket & Clip Body Material	Glass-Filled Polyester
--	------------------------

Contact Features

Terminal Length	26.31 mm
Contact Plating Material	Tin
Contact Base Material	Spring Brass
Relay Accessory, Socket & Clip Socket Type	DIN Rail Mount
Pole Configuration	2

Termination Features

Number of Pins	8
----------------	---

Mechanical Attachment

Relay Accessory, Socket & Clip Mounting Type	DIN Rail Snap Mount
--	---------------------

Operation/Application

Relay Accessory, Socket & Clip For Use With	K10 Relays
---	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1393144-7
K10P-11D15-24=K10/K20



TE Part # 4-1393144-0
K10P-11A15-120=K10/K20



TE Part # 5-1393144-4
K10P-11D15-110=K10/K20



TE Part # 3-1393144-9
K10P-11A15-12=K10/K20



TE Part # 4-1393144-1
K10P-11A15-24=K10/K20



TE Part # 5-1393144-5
K10P-11D15-12=K10/K20



TE Part # 4-1393144-2
K10P-11A15-240=K10/K20



TE Part # 4-1393144-4
K10P-11A15-6=K10/K20



TE Part # 5-1393144-9
K10P-11D15-48=K10/K20



TE Part # 6-1393144-0
K10P-11D15-6=K10/K20



TE Part # 5-1393144-6
K10P-11D15-120=K10/K20



TE Part # 2-1393144-1
K10L-11A15-120=K10/K20




TE Part # 4-1393144-3
K10P-11A15-48=K10/K20



TE Part # 1393145-4
K10P-7AT5-120=K10/K20

TE Part # 5-1393159-1
20C426=SPRING,HOLD-DOWN,K10,,0

Also in the Series | **Potter & Brumfield K10**



Power Relays(27)



Relay Accessories, Sockets & Clips(3)

Documents



CAD Files

Customer View Model

[ENG_CVM_CVM_2-1419106-7_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-1419106-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1419106-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

K10 Sockets & Accessories

English

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English