




Nanonics

TE Internal #: 2-1589946-6

Microminiature & Nanominiature D Connectors, Plug, Wire-to-Board, 25 Position, .025 in [635 mm] Centerline, Wire & Cable, Cable Mount (Free-Hanging)

[View on TE.com >](#)

Connectors > D-Shaped Connectors > Microminiature & Nanominiature D Connectors



Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **25**

Mounting Hardware: **Without**

Centerline (Pitch): **635 mm [ .025 in ]**

**Features**

**Product Type Features**

Product Type	Connector
Wire Type	Stranded
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Preloaded	Yes
Number of Positions	25

**Contact Features**

Contact Current Rating (Max)	1 A
------------------------------	-----

**Mechanical Attachment**

Mounting Hardware	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

**Housing Features**

Housing Material	Aluminum
Centerline (Pitch)	635 mm[.025 in]

**Usage Conditions**

Operating Temperature Range	-200 – 200 °C[-328 – 392 °F]
-----------------------------	------------------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

### Product Drawings

[STL025PC2DC024N = Wdualobe](#)

English

STL025PC2DC024N

Microminiature & Nanominiature D Connectors, Plug, Wire-to-Board, 25 Position, .025 in [635 mm] Centerline, Wire & Cable, Cable Mount (Free-Hanging)



[Datasheets & Catalog Pages](#)

[1589472 Nanonics Cross Reference](#)

English