




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM CU SERIES MULTI-FUNCTION INLET FI



Filter Type: **Power Entry Module**
Input Voltage Selection: **None**
Filter Switch Type: **SPST**
Filter Shield Type: **Shielded**
Filter Safety Features: **Shrouded Output**

All CORCOM CU SERIES MULTI-FUNCTION INLET FI (19)

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry Module
Filter Switch Type	SPST
Filter Input Termination Type	IEC
Filter Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Fuse Options	None
--------------	------

Electrical Characteristics

Input Voltage Selection	None
-------------------------	------



Leakage Current (Max) (120VAC, 60Hz)	250 µA
Leakage Current (Max) (250VAC, 50Hz)	400 µA
Filter Current Rating	15 A
Voltage Rating (Max)	250 VAC

Body Features

Filter Shield Type	Shielded
--------------------	----------

Mechanical Attachment

Mount Angle	Vertical
Filter Mount Style	Snap-In

Housing Features

Low Profile	Yes
-------------	-----

Dimensions

Panel Thickness Range	.63 – 2.1 mm [.024 – .08 in]
-----------------------	------------------------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Operation/Application

Filter Safety Features	Shrouded Output
For Use With	14 AWG Power Cord

Other

Comment	15A versions tested by Underwriters Laboratories to US and Canadian requirements and are VDE approved to 10A @ 250 VAC.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C8114-C8911
CORCOM CU SERIES MULTI-FUNCTION INLET FI

Also in the Series | Corcom CU

IEC Unfiltered Inlets(4)

Multi-Function Inlet Filters(19)

Documents

Product Drawings

15CUFS1=F8302

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1609114-1_E.3d_stp.zip



English

Customer View Model

[ENG_CVM_CVM_2-1609114-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1609114-1_E.3d_igs.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_Corcom_Product_Guide_CU_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[CORCOM_CU_SERIES](#)

English