

2-1609114-5 ✓ ACTIVE

[Corcom](#) | [Corcom CU](#)

TE Internal #: 2-1609114-5

Multi-Function Inlet Filters, Power Entry Module, None Input, SPST, Complete Shield, Shrouded Output, Vertical, 10 A, Flanged / Panel, Corcom CU

[View on TE.com >](#)



[EMI & EMC Solutions](#) > [EMI Filters](#) > [Multi-Function Inlet Filters](#) > [CORCOM CU SERIES MULTI-FUNCTION INLET FI](#)



Filter Type: **Power Entry Module**

Input Voltage Selection: **None**

Filter Switch Type: **SPST**

Filter Shield Type: **Complete Shield**

Filter Safety Features: **Shrouded Output**

[All CORCOM CU SERIES MULTI-FUNCTION INLET FI \(19\)](#)

## Features

### Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry Module
Filter Switch Type	SPST
Filter Input Termination Type	IEC
Filter Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

### Configuration Features

Fuse Options	None
--------------	------

### Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	250 $\mu$ A
Leakage Current (Max) (250VAC, 50Hz)	400 $\mu$ A
Filter Current Rating	10 A
Voltage Rating (Max)	250 VAC

### Body Features



Filter Shield Type	Complete Shield
--------------------	-----------------

### Mechanical Attachment

Mount Angle	Vertical
Filter Mount Style	Flanged, Panel

### Housing Features

Low Profile	Yes
-------------	-----

### Dimensions

Panel Thickness Range	.63 – 2.1 mm [.024 – .08 in]
-----------------------	------------------------------

### Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

### Operation/Application

Filter Safety Features	Shrouded Output
For Use With	14 AWG Power Cord

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | Corcom CU



## Documents

### Product Drawings

[10CUFF1=F8306](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1609114-5\\_B.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1609114-5\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1609114-5\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE](#)



English

[1654001\\_Corcom\\_Product\\_Guide\\_CU\\_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1\\_CORCOM\\_EMI\\_RFI\\_QRG](#)

English

[CORCOM\\_CU\\_SERIES](#)

English