

2-160983-1 ✓ ACTIVE

AMP-TY


TE Internal #: 2-160983-1

Cable Ties, Standard, Bag, 550 Newton Tensile Strength, 123.65 lbf Tensile Strength, Product Length 14.4 in [365 mm], Product Width .307 in [7.8 mm]

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Packaging Method: **Bag**

Tensile Strength: **550 Newton**

Product Length: **365 mm [ 14.4 in ]**

### Features

#### Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	550 Newton

#### Body Features

Primary Product Color	Natural
Primary Product Material	Polyamide 6.6 GF

#### Dimensions

Bundle Range Diameter	100 mm[3.93 in]
Product Length	365 mm[14.4 in]
Product Width	7.8 mm[.307 in]
Product Thickness	1.8 mm[.07 in]

#### Packaging Features

Packaging Method	Bag
Packaging Quantity	100

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-T3437-K1  
K-Type Tie-On Markers



TE Part # CAT-T3437-Z1  
Z-Type Push-On Markers



TE Part # EC4942-000  
11310000



TE Part # EC4943-000  
11320000



TE Part # EC4941-000  
11300000

## Documents

[Product Drawings](#)  
[CABLE TY 365X7.8 NAT](#)

English



---

**Datasheets & Catalog Pages**

**Connectivity Solutions for Industrial Applications**

English

**CABLE TIES**

English