

Kilovac

TE Internal #: 2-1618058-1

Protective Relays, 2 Form C, DPDT, 2 C/O, 5 A, 100 – 140 VAC

Input, 100 – 200 VDC Input, Snap-On DIN Rail, Three Phase

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Protective Relays



Protective Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**

Protective Relay Contact Current Rating: **5 A**

Protective Relay Input Voltage: **100 – 200 VDC**

Time Delay: **Without**

Features

Product Type Features

Time Delay	Without
Phase	Three

Electrical Characteristics

Protective Relay Input Voltage	100 – 200 VDC
--------------------------------	---------------

Contact Features

Protective Relay Contact Arrangement	2 Form C, DPDT, 2 C/O
Protective Relay Contact Current Rating	5 A

Mechanical Attachment

Protective Relay Mounting Type	Snap-On DIN Rail
--------------------------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1618058-1
WD25-001=RELAY, PARALLELING 24

TE Part # 1-1618058-6
WD32-001=RELAY, REV PWR, 24V

TE Part # 1-1618058-7
WD32-002=RELAY, REV PWR, 15V

TE Part # 1-1618058-8
WD32-003=RELAY, REV PWR, 120V

TE Part # 1-1618058-9
WD32-011=RELAY, REV KVAR, 24V

TE Part # 2-1618058-0
WD32-012=RELAY, REV KVAR, 15V

Documents

Product Drawings

WD32-013=RELAY, REV KVAR, 120V

English

Datasheets & Catalog Pages

5-1773450-5_sec11_KILOVAC_WD

English

