

2-1609114-2 ✓ ACTIVE

Corcom | Corcom CU


TE Internal #: 2-1609114-2

Multi-Function Inlet Filters, Power Entry Module, None Input, SPST, Complete Shield, Shrouded Output, Vertical, 1 A, Panel / Flanged, Corcom CU

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM CU SERIES MULTI-FUNCTION INLET FI



Filter Type: **Power Entry Module**

Input Voltage Selection: **None**

Filter Switch Type: **SPST**

Filter Shield Type: **Complete Shield**

Filter Safety Features: **Shrouded Output**

[All CORCOM CU SERIES MULTI-FUNCTION INLET FI \(19\)](#)

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry Module
Filter Switch Type	SPST
Filter Input Termination Type	IEC
Filter Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Fuse Options	None
--------------	------

Electrical Characteristics

Input Voltage Selection	None
-------------------------	------



Leakage Current (Max) (120VAC, 60Hz)	250 μ A
--------------------------------------	-------------

Leakage Current (Max) (250VAC, 50Hz)	400 μ A
--------------------------------------	-------------

Filter Current Rating	1 A
-----------------------	-----

Voltage Rating (Max)	250 VAC
----------------------	---------

Body Features

Filter Shield Type	Complete Shield
--------------------	-----------------

Mechanical Attachment

Mount Angle	Vertical
-------------	----------

Filter Mount Style	Flanged, Panel
--------------------	----------------

Housing Features

Low Profile	Yes
-------------	-----

Dimensions

Panel Thickness Range	.63 – 2.1 mm [.024 – .08 in]
-----------------------	------------------------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Operation/Application

Filter Safety Features	Shrouded Output
------------------------	-----------------

For Use With	18 AWG Power Cord
--------------	-------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom CU



Documents

Product Drawings

1CUFF1=F8303

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-1609114-2_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-1609114-2_B.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_CVM_2-1609114-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_Corcom_Product_Guide_CU_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[CORCOM_CU_SERIES](#)

English