

2-160971-1 ✓ ACTIVE

AMP-TY


TE Internal #: 2-160971-1

Cable Ties, Standard, Bag, 130 Newton Tensile Strength, 29.2 lbf Tensile Strength, Product Length 5.5 in [140 mm], Product Width .141 in [3.6 mm]

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Packaging Method: **Bag**

Tensile Strength: **130 Newton**

Product Length: **140 mm [5.5 in]**

Features

Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	130 Newton

Body Features

Primary Product Color	Natural
Primary Product Material	Polyamide 6.6 GF

Dimensions

Bundle Range Diameter	35 mm[1.37 in]
Product Length	140 mm[5.5 in]
Product Width	3.6 mm[.141 in]
Product Thickness	1.12 mm[.044 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-T3437-H85999 High Temperature Markers, HTC-M-SCE-TP</p>	 <p>TE Part # CAT-T3437-C6298 CM-SCE-TP Military Grade Markers</p>	 <p>TE Part # CAT-T3437-K1 K-Type Tie-On Markers</p>	 <p>TE Part # CAT-T3437-Z1 Z-Type Push-On Markers</p>
 <p>TE Part # 7175170001 CM-SCE-1/2-4H-4</p>	 <p>TE Part # 6622650001 CM-SCE-1/2-6H-4</p>	 <p>TE Part # 0076930001 CM-SCE-1/2-4H-9</p>	 <p>TE Part # 0325090001 CM-SCE-1/2-6H-9</p>



TE Part # 9305490001
HTCM-SCE-1/2-4H-4



TE Part # 0479490001
HTCM-SCE-1/2-4H-9



TE Part # EJ0826-000
CM-SCE-TP-1/4-4H-6



TE Part # EL8598-000
CM-SCE-TP-1/2-6H-3



TE Part # EL8599-000
CM-SCE-TP-1/2-6H-1



TE Part # EL8600-000
CM-SCE-TP-1/2-6H-5



TE Part # A81411-000
HTCM-SCE-TP-1/2-6H-4



TE Part # 6101810001
CM-SCE-1/4-4H-4



TE Part # 6485470001
CM-SCE-1/4-4H-9



TE Part # EC4942-000
11310000



TE Part # EC4943-000
11320000



TE Part # 3576550001
HTCM-SCE-1/4-4H-9

Documents

Product Drawings

[CABLE TY 140X3.6 NAT](#)

English

Datasheets & Catalog Pages

[Connectivity Solutions for Industrial Applications](#)

English

[CABLE TIES](#)

English