




**Buchanan**

TE Internal #: 2-1986722-2

PCB Terminal Blocks, Plug, Wire-to-Board, 22 Position, .15 in [3.81 mm] Centerline, 1 Row, Top Wire Entry Angle, 30 – 14 AWG Wire Size

[View on TE.com >](#)

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **22**

Centerline (Pitch): **3.81 mm [.15 in]**

Number of Rows: **1**

**Features**

**Product Type Features**

Wire Protection	With
Block Type	Spring Terminal Block
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board

**Configuration Features**

Threaded Flange	Without
Stacking Configuration	Side Stackable
Number of Positions	22
Number of Rows	1
Wire Entry Angle	Top

**Electrical Characteristics**

Current Rating (Max)	9 A, 11 A
Voltage Rating	300 VAC

**Body Features**



Interlock	Without
-----------	---------

Lever Color	Orange
-------------	--------

### Contact Features

Contact Mating Area Plating Material	Tin
--------------------------------------	-----

Contact Base Material	Copper Alloy
-----------------------	--------------

Contact Current Rating (Max)	11 A
------------------------------	------

### Mechanical Attachment

Mating Angle	90° (Bottom)/ 270° (Top)
--------------	--------------------------

Screwless Terminal Block	Yes
--------------------------	-----

Mounting Angle	Vertical
----------------	----------

Screw Flange	Without
--------------	---------

### Housing Features

Housing Color	Green
---------------	-------

Housing Material	PA 66
------------------	-------

Centerline (Pitch)	3.81 mm [.15 in]
--------------------	------------------

### Dimensions

Wire Size	.05 – 2 mm <sup>2</sup>
-----------	-------------------------

### Usage Conditions

Operating Temperature Range	-40 – 65 °C [-40 – 149 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Packaging Features

Packaging Quantity	25
--------------------	----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2018 (191)
--	---

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

## Product Drawings

STR PLUG SPRING TYPE LH 22P, 3.81mm

English

## CAD Files

3D PDF

3D

## Customer View Model

ENG\_CVM\_CVM\_2-1986722-2\_A.2d\_dxf.zip

English

## Customer View Model

ENG\_CVM\_CVM\_2-1986722-2\_A.3d\_igs.zip

English

## Customer View Model

ENG\_CVM\_CVM\_2-1986722-2\_A.3d\_stp.zip

English

2-1986722-2

PCB Terminal Blocks, Plug, Wire-to-Board, 22 Position, .15 in [3.81 mm] Centerline, 1 Row, Top Wire Entry Angle, 30 – 14 AWG Wire Size



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

[2-1773464-1\\_Spring\\_Type\\_Straight\\_Plugs](#)

English