



LUMAWISE | LUMAWISE LED Holders

TE Internal #: 2-2154857-3


LED Holders, Samsung LC040B / Samsung LC013B / Citizen

CLL340, Not Optic Compatible / Does Not Enable Zhaga

Compatibility, LUMAWISE LED Holders

[View on TE.com >](#)

Connectors > Lighting Connectors > LED Holders



Compatible LED: Citizen CLL330, Citizen CLL340, Cree CXA 35xx, Samsung LC013B, Samsung LC026B, Samsung LC040B

Lighting Connector Features Included: Does Not Enable Zhaga Compatibility, Not Optic Compatible

Operating Voltage: 250 VDC

Termination Method to Wire & Cable: Poke-In

COB Substrate Thickness: 1 mm

### Features

#### Product Type Features

Product Type	LED Holder
COB Substrate Thickness	1 mm
Connector System	Wire-to-Component
Sealable	No
Connector & Contact Terminates To	Wire & Cable

#### Configuration Features

Lighting Connector Features Included	Does Not Enable Zhaga Compatibility, Not Optic Compatible
Number of Positions	2

#### Electrical Characteristics

Current Rating (Max)	3 A
Operating Voltage	250 VDC

#### Body Features

Compatible LED	Citizen CLL330, Citizen CLL340, Cree CXA
----------------	--



35xx, Samsung LC013B, Samsung LC026B,  
Samsung LC040B

### Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	3 A

### Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

### Housing Features

Housing Material	PBT GF
------------------	--------

### Usage Conditions

Operating Temperature Range	-40 – 105 °C
-----------------------------	--------------

### Operation/Application

Circuit Application	Power
---------------------	-------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | LUMAWISE LED Holders



## Documents

### Product Drawings

Socket, SCALABLE LED, 2PC, Gold, w/TS

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2154857-3\\_A\\_c-2-2154857-3-a.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2154857-3\\_A\\_c-2-2154857-3-a.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2154857-3\\_A\\_c-2-2154857-3-a.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1-1773700-3\\_LED HOLDER\\_TYPE\\_CITIZEN](#)



English

[1-1773706-3\\_SCALABLEOVERVIEW\\_BROCHURE](#)

English

[8-1773700-8\\_SCALABLELEDHOLDER\\_APPNOTE](#)

English

[8-1773700-9\\_LEDBROCHURE](#)

English

[8-1773700-9\\_LEDBROCHURE](#)

Japanese

---

### Product Specifications

[Application Specification](#)

English

---

### Agency Approvals

[UL Report](#)

English