

CHAMP

TE Internal #: 2-5175887-4

TE Internal Description: CHAMP 050-2 REC ASSY V 26P

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors

Connector & Housing Type: **Receptacle**Number of Positions: **26**Centerline (Pitch): **1.27 mm [.05 in]**Number of Rows: **2**Row-to-Row Spacing: **1.9 mm [.075 in]****Features****Product Type Features**

Shell Type	Full Metal Shell
Frame Material	Die Cast Zinc
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board
Connector Type	Header
Product Type	Connector

Configuration Features

Number of Positions	26
Number of Rows	2
PCB Mount Orientation	Vertical
Preloaded	Yes

Body Features

Frame Plating Material	Nickel
Connector Profile	Standard
Color	Black
Shell Plating Material	Nickel
Shield Material	Steel
Shell Material	Steel
Shield Plating Material	Nickel over Copper

Contact Features

Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
	30 μ m

Termination Features

Termination Post Length	3.1 mm[.122 in]
-------------------------	-----------------

Mechanical Attachment

Panel Mount Feature	With
PCB Mount Retention	Without
Mating Retention	With
Mating Retention Type	Latch
Mounting Angle	Vertical
Mounting Hole Diameter	2.8 mm

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	Thermoplastic
Housing Color	Black

Dimensions

Row-to-Row Spacing	1.9 mm[.075 in]
Panel Thickness	2.01 mm[.079 in]
PCB Thickness (Recommended)	1.6 mm[.062 – .093 in]

Usage Conditions

Housing Material Temperature	Standard
------------------------------	----------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
Packaging Quantity	12

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_2-5175887-4_O.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-5175887-4_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-5175887-4_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[CHAMP 050 II Shield Case Kit \(Original Type\)](#)

English

[Application Specification](#)



English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English