

2-55825-1 ✓ ACTIVE



TE Internal #: 2-55825-1

Splices, 16 – 14 AWG Wire Size, 1.25 – 2 mm² Wire Size, Sealable, .19 in [4.83 mm] Barrel Inside Diameter, 2050 – 5180 CMA Wire Size, Copper, Blue

[View on TE.com >](#)

Terminals & Splices > Splices



Wire Size: 1.25 – 2 mm²

Sealable: **Yes**

Accepts Wire Insulation Diameter Range: 4.83 mm [.19 in]

Barrel Inside Diameter: 4.83 mm [.19 in]

Features

Product Type Features

Sealable	Yes
Splice Type	Butt Splice
Serrated	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Insulation Sleeve Material	Polyolefin
Weight per Piece	1.456 g
Plating Material	Tin, Unplated
Primary Product Material	Copper
Primary Product Color	Blue

Contact Features

Contact Plating Material	Tin
--------------------------	-----



Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Accepts Wire Insulation Diameter Range	4.83 mm[.19 in]
Barrel Inside Diameter	4.83 mm[.19 in]
Overall Product Length	40.79 mm[1.606 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	2500
Packaging Method	Tape Mounted

Other

Military Category	No
-------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 69710-1
 C-HEAD FRAME W/O DIES



TE Part # 55825-1
 16-14 PRE-INSUL SEALED SPLICE




TE Part # 8-55825-2
 16-14 PRE-INSUL SEALED SPLICE



TE Part # 69120-2
 HYP8 220V HEAVY DUTY ELECTRIC PUMP



TE Part # 1490748-1
 HYP10 MANUAL TOOL



TE Part # 68068
 PNEU HAND TOOL

Documents

Product Drawings

16-14 PRE-INSUL SEALED SPLICE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-55825-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-55825-1_K.3d_stp.zip](#)

2-55825-1

Splices, 16 – 14 AWG Wire Size, 1.25 – 2 mm² Wire Size, Sealable, .19 in [4.83 mm]
Barrel Inside Diameter, 2050 – 5180 CMA Wire Size, Copper, Blue



English

Customer View Model

[ENG_CVM_CVM_2-55825-1_K.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English