



PIDG

TE Internal #: 326859


Ring Terminals & Spade Terminals, Spade Tongue, 12 – 10 AWG

Wire Size, 2.62 – 6.64 mm² Wire Size, 5180 – 13100 CMA Wire Size,

PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG Spade Tongue Terminals



Ring & Spade Terminal Type: **Spade Tongue**

Wire Size: **5180 – 13100 CMA**

Stud Size: **#6, M3.5**

[All PIDG Spade Tongue Terminals \(64\)](#)

Features

Product Type Features

|                                        |                    |
|----------------------------------------|--------------------|
| Shape Description                      | SPADE-020          |
| Stud Size                              | #6, M3.5           |
| Sealable                               | No                 |
| Wire Insulation Support Retention Type | Insulation Support |

Configuration Features

|                |       |
|----------------|-------|
| Terminal Angle | 180 ° |
|----------------|-------|

Electrical Characteristics

|               |       |
|---------------|-------|
| Voltage (Max) | 300 V |
|---------------|-------|

Body Features

|                  |         |
|------------------|---------|
| Inspection Slot  | No      |
| Weight per Piece | 2.373 g |

Contact Features

|                            |              |
|----------------------------|--------------|
| Ring & Spade Terminal Type | Spade Tongue |
|----------------------------|--------------|



|                           |          |
|---------------------------|----------|
| Barrel Type               | Closed   |
| Terminal Orientation      | Straight |
| Terminal Plating Material | Tin      |

Mechanical Attachment

|                         |      |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Dimensions

|                                        |                              |
|----------------------------------------|------------------------------|
| Wire Size                              | 5180 – 13100 CMA             |
| Stud Diameter                          | 3.68 mm[.145 in]             |
| Tongue Thickness                       | .79 mm[.031 in]              |
| Overall Product Length                 | 27.81 mm[1.095 in]           |
| Accepts Wire Insulation Diameter (Max) | 5.84 mm[.23 in]              |
| Accepts Wire Insulation Diameter Range | 3.81 – 5.84 mm[.15 – .23 in] |

Usage Conditions

|                             |                     |
|-----------------------------|---------------------|
| Insulation Option           | Partially Insulated |
| Operating Temperature Range | 105 °C[221 °F]      |

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |
| Heavy Duty                            | No     |

Industry Standards

|                      |    |
|----------------------|----|
| Government Qualified | No |
|----------------------|----|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Quantity | 500         |
| Packaging Method   | Loose Piece |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                              |
|-----------------------------------------------|----------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                    |
| EU ELV Directive 2000/53/EC                   | Compliant                                    |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold      |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224) |



Candidate List Declared Against: JUNE 2022 (224)  
Does not contain REACH SVHC

|                           |                                                                                     |
|---------------------------|-------------------------------------------------------------------------------------|
| Halogen Content           | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability                                        |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                    |                                                      |                                                      |                                                    |
|--------------------------------------------------------------------|------------------------------------------------------|------------------------------------------------------|----------------------------------------------------|
| <p>TE Part # 59824-1<br/>TETRA-CRIMP PIDG PG FASTON 22-10 ASSY</p> | <p>TE Part # 58433-3<br/>PRO CR ASSY, RBY IS9252</p> | <p>TE Part # 59239-4<br/>HHHT PIDG PG 12-10 ASSY</p> | <p>TE Part # 58423-1<br/>DIE, RBY IS9252</p>       |
| <p>TE Part # 539691-2<br/>ERGO DIE R.B.Y</p>                       | <p>TE Part # 2063030-1<br/>SDE DIESET, RBY, UL</p>   | <p>TE Part # 47808-6<br/>DIES PIDG 12-10 DIE SET</p> | <p>TE Part # 679300-1<br/>1210 PIDG CRIMP HEAD</p> |



TE Part # 169400  
CERTI-LOK FRAME W/O DIES

TE Part # 1-59239-4  
HHHT PIDG 16-10 HEAD

TE Part # 1SET191001R0000  
CRIMP-HT

TE Part # 1SET191002R0000  
TET CRIMP-HT

TE Part # 169404  
CERTI-LOK DIE

Also in the Series | PIDG

Compression Connectors(17)

Crimp Terminal Housings(1)

Crimp Wire Pins, Tabs & Ferrules(41)

Hand Crimping Tools(2)

Knife Disconnects(11)

PCB Terminals(9)

Quick Disconnects(53)

Ring Terminals & Spade Terminals(861)

Special Purpose Terminals(1)

Splices(48)

Documents



Product Drawings

TERMINAL,PIDG SPD 12-10 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_326859\_J.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_326859\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_326859\_J.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_326859\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_326859\_E.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_326859\_E.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PIDG TERMINALS & SPLICES Quick Reference Guide

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD\_326859\_10312017851\_dmtec

English

MD\_326859\_10312017851\_dmtec

English

Agency Approvals

UL Report

English



UL Report

English