

329331 ✓ ACTIVE

TE Internal #: 329331

RF Connector Ferrules, RG 196A, Brass, Zinc Plating, Accepts Wire

Insulation Diameter Range .84 – 1.5 mm [.033 – .059 in]

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Coax Accessories > Ferrules



Compatible With RF Cable Type: **RG 196A**

Ferrule Material: **Brass**

Ferrule Plating Material: **Zinc**

Accepts Wire Insulation Diameter Range: **.84 – 1.5 mm [.033 – .059 in]**

Features

Product Type Features

Compatible With RF Cable Type	RG 196A
-------------------------------	---------

Body Features

Primary Product Color	Violet
-----------------------	--------

Body Plating Material	Tin
-----------------------	-----

Contact Features

Ferrule Material	Brass
------------------	-------

Ferrule Plating Material	Zinc
--------------------------	------

Dimensions

Accepts Wire Insulation Diameter Range	.84 – 1.5 mm [.033 – .059 in]
--	-------------------------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[T-SHIELD,.033-.059](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_329331_V.2d_dxf.zip](#)

English

329331

RF Connector Ferrules, RG 196A, Brass, Zinc Plating, Accepts Wire Insulation
Diameter Range .84 – 1.5 mm [.033 – .059 in]



Customer View Model

[ENG_CVM_CVM_329331_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_329331_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1307191 RF Coax Products Catalog](#)

English