




PIDG

TE Internal #: 323011

Ring Terminals & Spade Terminals, Slotted Ring Tongue, 26 – 22 AWG Wire Size, .1 – .41 mm² Wire Size, 202 – 810 CMA Wire Size, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG Slotted Ring Tongue Terminals



Ring & Spade Terminal Type: **Slotted Ring Tongue**

Wire Size: **202 – 810 CMA**

Stud Size: **#6, M3.5**

[All PIDG Slotted Ring Tongue Terminals \(7\)](#)

Features

Product Type Features

Terminal Features	Slotted
Shape Description	Slotted Ring-001
Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Terminal Angle	180 °
----------------	-------

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Weight per Piece	.294 g

Contact Features

--	--



Ring & Spade Terminal Type	Slotted Ring Tongue
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Overall Product Length	18.26 mm[.719 in]
Accepts Wire Insulation Diameter (Max)	2.03 mm[.08 in]
Accepts Wire Insulation Diameter Range	1.27 – 2.03 mm[.05 – .08 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin
Heavy Duty	No

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content
 Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability
 Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

REPRESENTATION ONLY

TE Part # 46121
DAHT PG PIDG 26-22 ASSY

TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY

REPRESENTATION ONLY

TE Part # 169485
DAHT PIDG PG 26-22 ASSY

TE Part # 69344
PIDG 26-22 DIE SET

Also in the Series | PIDG

Compression Connectors(17)

Crimp Terminal Housings(1)

Crimp Wire Pins, Tabs & Ferrules(41)


Hand Crimping Tools(2)



Knife Disconnects(11)



PCB Terminals(9)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(861)



Special Purpose Terminals(1)



Splices(48)

Documents

Product Drawings

[TERMINAL,PIDG R SLTD 26-22 6](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_323011_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_323011_R.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_323011_R.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[UL Report](#)

323011

Ring Terminals & Spade Terminals, Slotted Ring Tongue, 26 – 22 AWG Wire Size, .1 – .41 mm² Wire Size, 202 – 810 CMA Wire Size, PIDG



English