



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **12**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Header
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	12
PCB Mount Orientation	Vertical
Number of Power Positions	12
Number of Rows	3

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
----------------	--------



Multiple Contact Types	Without
Contact Current Rating (Max)	10 A, 12 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 – .91 µm[30 – 36 µin]
Underplate Material Thickness	1.27 µm[50 µin]
Contact Termination Area Plating Thickness	2.54 µm[100 µin]

Termination Features

Termination Post & Tail Length	3.15 mm[.124 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	With
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Retention	With
Mating Retention Type	Positive Lock

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

Row-to-Row Spacing	6.35 mm[.25 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Width	20.32 mm[.8 in]
Length	26.67 mm[1.05 in]

Usage Conditions

--	--



Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Assembly Integration Feature	Without
Circuit Application	Power

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189
VDE Tested	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	75

Other

For Use With	Mates with Plug Housing (Using Socket Contacts)
--------------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 350735-1 12P UMNL PLUG HSG	 TE Part # 926681-3 12P UNIV.CAP HSG.	 TE Part # 926681-1 UNIV.M-N-L.CAP HSG.	 TE Part # 643428-2 12P UMNL HDR ASSY POL
 TE Part # 643428-3 12P UMNL HDR ASSY POL 94VO	 TE Part # 350812-1 STR/REL CLAMP UMNL	 TE Part # 794279-1 12P UMNL INTERFACE SEAL	 TE Part # 640717-1 12P UMNL STR/REL
 TE Part # 1-640723-0 12P UMNL STR/REL & INSRT NATL	 TE Part # 794280-1 12P UMNL WIRE SEAL	 TE Part # 1-350590-0 STR/REL CLAMP NATL	 TE Part # 770022-1 12P UMNLII IN-LNE PLUG HSG KIT
 TE Part # 1586854-1 12P UMNL CAP HSG, GW	 TE Part # 1-350848-2 12P UMNL PLUG TEST ASSY 94VO	 TE Part # 1863006-1 12P UMNL CAP HSG	 TE Part # 643255-1 12P UMNL ASSY MOD HSG VO



TE Part # 794727-1
12P UMNLCAP HSG NATL, BLACK

TE Part # 2178620-1
UMNLCAP 12 WAY

TE Part # 2178621-1
UMNLCAP 12 WAY

Also in the Series | Universal MATE-N-LOK

Circular Power Connectors(2)

Connector Contacts(11)

Insertion & Extraction Tools(4)

Power Contacts(207)

Rectangular Boots & Strain Relief(35)

Rectangular Connector Adapters(7)

Rectangular Connector Hardware(1)

Rectangular Connector Housings(2)

Rectangular Connector Keying Plugs(3)

Rectangular Connector Locking(4)

Rectangular Connector Seals(26)

Rectangular Power Connectors(728)

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_350713-4_M.2d_dxf.zip

English

Customer View Model



[ENG_CVM_350713-4_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_350713-4_M.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_350713-4_U.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_350713-4_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_350713-4_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[CSA Certificate](#)

English