




PIDG

TE Internal #: 36149  
Ring Terminals & Spade Terminals, Ring Tongue, 22 – 16 AWG  
Wire Size, .3 – 1.42 mm² Wire Size, 509 – 3260 CMA Wire Size, Stud  
Size M3.5 / #6, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG RING TONGUE TERMINALS



Ring & Spade Terminal Type: **Ring Tongue**  
Wire Size: **509 – 3260 CMA**  
Stud Size: **#6, M3.5**

[All PIDG RING TONGUE TERMINALS \(421\)](#)

Features

Product Type Features

|                                        |                    |
|----------------------------------------|--------------------|
| Shape Description                      | RING-041           |
| Stud Size                              | #6, M3.5           |
| Sealable                               | No                 |
| Wire Insulation Support Retention Type | Insulation Support |

Configuration Features

|                 |       |
|-----------------|-------|
| Number of Holes | 1     |
| Terminal Angle  | 180 ° |

Electrical Characteristics

|               |       |
|---------------|-------|
| Voltage (Max) | 300 V |
|---------------|-------|

Body Features

|                  |        |
|------------------|--------|
| Inspection Slot  | No     |
| Weight per Piece | .715 g |

Contact Features

|  |  |
|--|--|
|  |  |
|--|--|

|                            |             |
|----------------------------|-------------|
| Military Part Class        | Class I     |
| Ring & Spade Terminal Type | Ring Tongue |
| Barrel Type                | Closed      |
| Terminal Orientation       | Straight    |
| Terminal Plating Material  | Tin         |

Mechanical Attachment

|                         |      |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Dimensions

|                                        |                               |
|----------------------------------------|-------------------------------|
| Wire Size                              | 509 – 3260 CMA                |
| Stud Diameter                          | 3.68 mm[.145 in]              |
| Tongue Thickness                       | .79 mm[.031 in]               |
| Overall Product Length                 | 17.07 mm[.672 in]             |
| Accepts Wire Insulation Diameter (Max) | 3.18 mm[.125 in]              |
| Accepts Wire Insulation Diameter Range | 2.03 – 3.18 mm[.08 – .125 in] |

Usage Conditions

|                             |                     |
|-----------------------------|---------------------|
| Insulation Option           | Partially Insulated |
| Operating Temperature Range | 105 °C[221 °F]      |

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |
| Heavy Duty                            | No     |

Industry Standards

|                      |     |
|----------------------|-----|
| Government Qualified | Yes |
|----------------------|-----|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Quantity | 5000        |
| Packaging Method   | Loose Piece |

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                               |
| EU ELV Directive 2000/53/EC                   | Compliant                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |


|                                        |                                                                                                                                 |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                        | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability              | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                        |                                                                                                                                        |                                                                                                                                            |                                                                                                                                            |
|--------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 59824-1<br/>TETRA-CRIMP PIDG PG FASTON 22-10 ASSY</p> |  <p>TE Part # 47386<br/>DAHT PG PIDG 26-16 ASSY</p> |  <p>TE Part # 47386-4<br/>DAHT PG PIDG 26-16 ASSY</p> |  <p>TE Part # 58433-3<br/>PRO CR ASSY, RBY IS9252</p> |
|  <p>TE Part # 59250<br/>T-HEAD PIDG 26-14 ASSY</p>                  |  <p>TE Part # 58423-1<br/>DIE, RBY IS9252</p>       |  <p>TE Part # 525690<br/>DAHT PG PIDG 20-18 ASSY</p>  |  <p>TE Part # 539691-2<br/>ERGO DIE R.B.Y</p>         |

|                                                                                                                                      |                                                                                                                                        |                                                                                                                                          |                                                                                                                                          |
|--------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 2063030-1<br/>SDE DIESET, RBY, UL</p> |  <p>TE Part # 47806-2<br/>DIES PIDG 22-16 DIE SET</p> |  <p>TE Part # 59300<br/>T-HEAD PIDG PG 26-16 ASSY</p> |  <p>TE Part # 169400<br/>CERTI-LOK FRAME W/O DIES</p> |
|  <p>TE Part # 1SET191001R0000<br/>CRIMP-HT</p>      |  <p>TE Part # 1SET191002R0000<br/>TET CRIMP-HT</p>   |  <p>TE Part # 169404<br/>CERTI-LOK DIE</p>           |                                                                                                                                          |

Also in the Series | PIDG

|                                                                                                                         |                                                                                                                       |                                                                                                                                       |                                                                                                                                        |
|-------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
|  <p>Compression Connectors(17)</p>   |  <p>Crimp Terminal Housings(1)</p> |  <p>Crimp Wire Pins, Tabs &amp; Ferrules(41)</p> |  <p>Hand Crimping Tools(2)</p>                    |
|  <p>Knife Disconnects(11)</p>        |  <p>PCB Terminals(9)</p>           |  <p>Quick Disconnects(53)</p>                    |  <p>Ring Terminals &amp; Spade Terminals(861)</p> |
|  <p>Special Purpose Terminals(1)</p> |  <p>Splices(48)</p>                |                                                                                                                                       |                                                                                                                                        |

Documents



Product Drawings

PIDG R 22-16 COMM 22-18 MIL 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_36149\_AA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_36149\_AA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_36149\_AA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PIDG TERMINALS & SPLICES Quick Reference Guide

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD\_36149\_05022015453\_dmtec

English

MD\_36149\_05022015453\_dmtec

English

Agency Approvals

UL Report

English

UL Report

English