

371176-000 ✓ ACTIVE

RAYCHEM

TE Internal #: 371176-000

Splices, Sealable, 2000 – 4000 CMA Wire Size, Length 30.15 mm [1.187 in], Bag, Fully Insulated, -55 – 150 °C [-67 – 302 °F]

[View on TE.com >](#)



Terminals & Splices > Splices



Sealable: **Yes**

Accepts Wire Insulation Diameter Range: **2.8 mm [.11 in]**

Wire Size: **2000 – 4000 CMA**

Overall Product Length: **30.15 mm [1.187 in]**

Government Qualified Splice: **No**

## Features

### Product Type Features

Sealable	Yes
----------	-----

### Dimensions

Accepts Wire Insulation Diameter Range	2.8 mm[.11 in]
Wire Size	2000 – 4000 CMA
Overall Product Length	30.15 mm[1.187 in]

### Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

### Operation/Application

Heavy Duty	No
------------	----

### Industry Standards

Government Qualified Splice	No
-----------------------------	----

### Packaging Features

Packaging Method	Bag
------------------	-----

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUL 2021 (219)

SVHC &gt; Threshold:

Pb (37% in Solder)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl &lt; 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # CJ2087-000  
HL2010E-KIT-120V

## Documents

### Product Drawings

[D-1744-02](#)

English

### Datasheets & Catalog Pages

[Harness Repair Products Quick Reference Guide](#)

English



---

## Product Specifications

### Product Specification

English

### Installation Procedure for Products Designed for In-Line Splice Installed with Hot Air Gun

English