



CII

TE Internal #: 3-1437468-3

Time Delay Relays, Knob, 120 VAC Input, 120 VDC Input, 10A@120VAC A, On-Delay, 6 – 180 seconds Delay Time, Socket

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Knob**

Time Delay Relay Input Voltage: **120 VDC**

Time Delay Relay Contact Current Rating: **10A@120VAC A**

Mode of Operation: **On-Delay**

**Features**

**Product Type Features**

Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

**Configuration Features**

Multiple Timing Ranges	Without
------------------------	---------

**Electrical Characteristics**

Actuating System	AC/DC
Time Delay Relay Input Voltage	120 VDC

**Contact Features**

Contact Arrangement	2 Form C, DPDT, 2 C/O
Type of Control	Knob
Time Delay Relay Contact Current Rating	10A@120VAC A
Delay Time	6 – 180 seconds

**Termination Features**

Termination Type	8 Pin Octal Type Plug
------------------	-----------------------

**Mechanical Attachment**

Time Delay Relay Mounting Type	Socket
--------------------------------	--------

### Dimensions

Dimensions (L x W x H) (Approximate)	50 x 50 x 83 mm[1.97 x 1.97 x 3.27 in]
--------------------------------------	----------------------------------------

### Usage Conditions

Operating Temperature Range	-30 – 50 °C
-----------------------------	-------------

### Operation/Application

Mode of Operation	On-Delay
-------------------	----------

### Other

Repeatability (Max)	±.5% +4 msec
---------------------	--------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



## Documents

### Product Drawings

[SCCLA012XXAFXA=6/180SEC01TIMER](#)

English

---

### Datasheets & Catalog Pages

[5-1773450-5\\_sec12\\_SCB\\_SCC](#)

English