

353746-1 ✓ ACTIVE

AMP

TE Internal #: 353746-1

Other Automotive Connector Accessories, Ferrite, Wire-to-Wire /  
Wire-to-Board, Other, Natural, -40 – 221 °F [-40 – 105 °C]

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories



Automotive Connector Accessory Type: **Ferrite**

Connector System: **Wire-to-Board, Wire-to-Wire**

Primary Product Material: **Other**

Primary Product Color: **Natural**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

## Features

### Product Type Features

Automotive Connector Accessory Type	Ferrite
Connector System	Wire-to-Board, Wire-to-Wire

### Body Features

Primary Product Material	Other
Primary Product Color	Natural

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Industry Standards

Industry Standard	JASO, JIS
-------------------	-----------

### Packaging Features

Packaging Quantity	200
Packaging Method	Bag

## Product Compliance





[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 353744-7 SQUIB AIRBAG/HSG-MAIN</p>	 <p>TE Part # 353745-7 SQUIB AIRBAG/HSG-LID</p>	 <p>TE Part # 353745-2 FIX-IN SQUIB CONN HSG-LID BK</p>
---	--	--

## Documents

**Product Drawings**  
SQUIB AIRBAG /FERRITE

Japanese

**CAD Files**  
3D PDF



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_353746-1\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_353746-1\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_353746-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Product Specification](#)

Japanese

[Product Specification](#)

Japanese

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English