

3-1991253-7 ✓ ACTIVE

AMPLIMITE


TE Internal #: 3-1991253-7

D-Sub Backshells & Clamps, Backshell, Clam Shell, 37 Position, Size 4, Cable Exit Angle 180° (In-Line), Wire & Cable

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Backshell**

Cable Clamp Type: **Clam Shell**

Number of Positions: **37**

Compatible With Connector Shell Size: **4**

Shielded: **No**

### Features

#### Product Type Features

Clam Shell Length	Standard
Grommets	Without
Slide Latch	Without
Product Type	Accessory
D-Shaped Connector Accessories	Backshell
Connector & Contact Terminates To	Wire & Cable

#### Configuration Features

Number of Positions	37
---------------------	----

#### Body Features

Shield Plating Material	None
Cable Clamp Material	Carbon Steel
Color	Black
Backshell Material	Polyamide
Cable Clamp Type	Clam Shell



Cable Exit Angle	180° (In-Line)
------------------	----------------

### Mechanical Attachment

Screw & Hole Thread Size	4-40
--------------------------	------

### Dimensions

Cable Insulation Diameter Range	3 – 11 mm [.118 – .433 in]
---------------------------------	----------------------------

### Operation/Application

Compatible With Connector Shell Size	4
--------------------------------------	---

Shielded	No
----------	----

### Industry Standards

Cover Flammability Rating	UL 94V-4
---------------------------	----------

### Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Box, Loose Piece
------------------	------------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

### Product Drawings

[37 WAY LOW COST D SUB BACKSHEL](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_3-1991253-7\\_A\\_c-3-1991253-7-a.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_3-1991253-7\\_A\\_c-3-1991253-7-a.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_3-1991253-7\\_A\\_c-3-1991253-7-a.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Product Specification](#)

English