




Connectors > Lighting Connectors > LED Holders



Compatible LED: **Soleriq E30**

Lighting Connector Features Included: **Does Not Enable Zhaga Compatibility, Not Optic Compatible**

Operating Voltage: **250 VDC**

Termination Method to Wire & Cable: **Poke-In**

Connector System: **Wire-to-Component**

Features

Product Type Features

Product Type	LED Holder
Connector System	Wire-to-Component
Sealable	No

Configuration Features

Lighting Connector Features Included	Does Not Enable Zhaga Compatibility, Not Optic Compatible
--------------------------------------	---

Electrical Characteristics

Current Rating (Max)	3 A
Operating Voltage	250 VDC

Body Features

Compatible LED	Soleriq E30
----------------	-------------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy



Contact Current Rating (Max)	3 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Housing Features

Housing Material	PBT GF
------------------	--------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 105 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 8-2834006-2
2P MRPK CONN_BK/WE

TE Part # 2324697-2
PUSH GRIP CONNECTOR 2P

TE Part # 2-2834245-1
2P, FLEX GRIP WIRE CONNECTOR

Also in the Series | LUMAWISE LED Holders

LED Holders(79)

Documents

Product Drawings

Socket, SCALABLE LED, 2PC, Tin, w/TS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2154857-3_A_c-3-2154857-3-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2154857-3_A_c-3-2154857-3-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2154857-3_A_c-3-2154857-3-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773700-6_LED HOLDER TYPE OSRAM

English

1-1773706-3_SCALABLEOVERVIEW_BROCHURE

English

8-1773700-8_SCALABLELEDHOLDER_APPNOTE



English

[8-1773700-9_LEDBROCHURE](#)

English

[8-1773700-9_LEDBROCHURE](#)

Japanese

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English