




Test Probe 130

TE Internal #: 3-582118-6

Test Probe Receptacles, Side Entry, Gold, Cable-to-Board, 1
Position, Printed Circuit Board, Power & Signal, Board Mount, Test
Probe 130

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Connector Accessories > Test Probe Receptacles



Profile Height from PCB: 5.84 mm [.23 in]
Funnel Entry: **Without**
Test Probe Hole Location: **Side Entry**
Contact Mating Area Plating Material: **Gold**
Connector System: **Cable-to-Board**

Features

Product Type Features

Funnel Entry	Without
Test Probe Hole Location	Side Entry
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
---------------------	---

Contact Features

Contact Base Material	Brass
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	4.75 A

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Dimensions

--	--



Profile Height from PCB	5.84 mm[.23 in]
-------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 3-582118-0 TEST PROBE REC130 BI BLK GPBR	 TE Part # 3-582118-9 TEST PROBE REC130 BI WHT GPBR	 TE Part # 3-582118-4 TEST PROBE REC130 BI YEW GPBR	 TE Part # 3-582118-2 TEST PROBE REC130 BI RED GPBR
 TE Part # 350180-2 TEST PROBE REC130L SPCL RED GPBR	 TE Part # 3-582118-5 TEST PROBE REC130 BI GRN GPBR	 TE Part # 3-582119-0 TEST PROBE REC130 TRI-MT BLK GPBR	 TE Part # 3-582119-9 TEST PROBE REC130 TRI-MT WHT GPBR
 TE Part # 3-582340-9 TEST PROBE REC130H BI-MT WHT GPBR	 TE Part # 350180-3 TEST PROBE REC130 SPCL RRN GPBR	 TE Part # 1-380736-9 TEST PROBE REC180 BI WHT GPBR	 TE Part # 1-521799-0 TEST PROBE HOUSING BLACK
 TE Part # 1-521799-2 TEST PROBE HOUSING RED	 TE Part # 1-521799-5 TEST PROBE HOUSING GREEN	 TE Part # 350180-5 TEST PROBE REC130 SPCL GRN GPBR	 TE Part # 350180-6 TEST PROBE REC130 SPCL BLU GPBR
 TE Part # 6-582118-9 TEST PROBE REC130 BI NAT GPBR			

Also in the Series | [Test Probe 130](#)



Test Probe Receptacles(21)

Documents

Product Drawings

TEST PROBE REC130 BI BLU GPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-582118-6_AP.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-582118-6_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-582118-6_AP.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English

Test Probe Receptacle Contacts

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English