




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **7**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable

Configuration Features

Number of Positions	7
Number of Power Positions	7
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Connector Profile	Standard
-------------------	----------

Contact Features

--	--



Contact Layout	Inline
Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7 A
Contact Retention Within Housing	With
Contact Type	Receptacle
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]
Underplate Material Thickness	30 µm[.762 µin]
Contact Termination Area Plating Thickness	2.03 – 5.08 µm[80 – 200 µin]

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
Wire/Cable Type	Discrete Wire
Wire Type	Stranded

Mechanical Attachment

Strain Relief	With
Mating Alignment	Without
Contact Retention Type Within Housing	Locking Lance
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	Without

Housing Features

Wire & Cable IDC Installation Type	Closed End
Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Red
Housing Material	Nylon
Cable Exit Angle	90°

Dimensions

Wire Size	.325 mm²
Accepts Wire Insulation Diameter Range	2.41 mm[.095 in]



Height	9.02 mm[.355 in]
Length	27.74 mm[1.092 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	250

Other

For Use With	MTA .156 Header
--------------	-----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58247-1 MTA 156 CRIMP HEAD REPAIR DISCRETE	TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME	TE Part # 640383-7 07P MTA156 HDR ASSY STR SQ SN	TE Part # 640388-7 07P MTA156 HDR ASSY RN STR F/L
TE Part # 643464-5 07P MTA156 HDR ASSY STR W/O#6	TE Part # 640387-7 07P MTA156 HDR ASSY SQ R/A	TE Part # 644752-7 07P MTA156 HDR ASSY SQ STR F/L	TE Part # 640445-7 07P MTA156 HDR ASSY FL/STR SN
TE Part # 643464-6 07P MTA156 HDR ASSY W/O#2,4,&6	TE Part # 643464-2 07P MTA156 HDR ASSY STR W/O#2	TE Part # 3-644615-7 07P MTA156 POL LOCK HDR TIN	TE Part # 640551-7 07P MTA156 COVER



 TE Part # 641991-5 07P MTA156 HDT SQ W/O#1,4,6	 TE Part # 643067-7 07P MTA156 MOLDED COVER	 TE Part # 643071-7 07P MTA156 FD-THRU COVER	 TE Part # 640384-7 07P MTA156 HDR ASSY STR RND SN
 TE Part # 641991-2 07P MTA156 HDR ASSY SQ W/O#5	 TE Part # 643464-4 07P MTA156 HDR ASSY STR W/O#3	 TE Part # 3-644617-7 07P MTA156 HDR ASY PO RA FB LF	 TE Part # 59804-1 MAINTENANCE TOOL

Also in the Series | MTA 156

 Insertion & Extraction Tools(1)	 PCB Connector Covers(92)	 PCB Connector Keying(2)	 PCB Connector Mounting(1)
 PCB Headers & Receptacles(729)	 Power Contacts(3)	 Rectangular Caps & Covers(1)	 Rectangular Power Connectors(749)
 Standard Rectangular Connectors (1309)	 Wire-to-Board Connector Contacts(12)		

Documents



Product Drawings

07P MTA156 CONN ASSY 22AWG RED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-640433-7_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-640433-7_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-640433-7_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MTA, CST-100 II, SL-156 and AMP Economy Power (EP) Connectors

English

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

CSA Certificate

English