

AMPLIMITE

TE Internal #: 443975-4

Box Mount D-Sub Connectors, Receptacle, Post Diameter .76 mm [.03 in], Vertical, Cable-to-Board, 37 Position, Size 4, Socket, Size 20

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors

Connector & Housing Type: **Receptacle**Post Diameter: **.76 mm [.03 in]**PCB Mount Orientation: **Vertical**Connector System: **Cable-to-Board**Number of Positions: **37****Features****Product Type Features**

Product Type	Connector
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
D-Sub Shell Size	4
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Blindmate	No

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	37
Power/Signal/Coax Combination	No

Body Features

Box Mount D-Sub Connector Insert Arrangement	MS18276-1
Shell Material	Steel
Shell Plating Material	Cadmium
Non-Magnetic	No

Contact Features

Contact Type	Socket
	10 µin



Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Brass
D-Sub Contact Size	20
Contact Current Rating (Max)	5 A

Termination Features

Termination Post Length	3.95 mm[.156 in]
-------------------------	------------------

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Dimensions

Post Diameter	.76 mm[.03 in]
---------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

ULTRA-LITE Connector	No
Circuit Application	Signal

Industry Standards

NASA Qualification	No
--------------------	----

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	For solder dip product see part number 443975-9.
---------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022
(224)

Candidate List Declared Against: JAN 2022
(223)

SVHC > Threshold:

Cd (99.5% in Component Part Plating)

Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

Product Drawings

[AMPLIMITE,RCPT ASY,POSTD,109,4](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_443975-4_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_443975-4_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_443975-4_F.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model



[ENG_CVM_443975-4_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_443975-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_443975-4_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[UL Report](#)

English