




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **3 mm [.118 in]**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Header Type                       | Fully Shrouded        |
| Rectangular Power Connector Type  | Header                |
| Connector & Housing Type          | Plug                  |
| Connector System                  | Wire-to-Board         |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

|                           |             |
|---------------------------|-------------|
| Number of Positions       | 4           |
| PCB Mount Orientation     | Right Angle |
| Number of Power Positions | 4           |
| Number of Rows            | 2           |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 250 VDC |
|-------------------|---------|

Contact Features



|                                                |                  |
|------------------------------------------------|------------------|
| Contact Termination Area Plating Finish        | Matte            |
| Multiple Contact Types                         | Without          |
| Contact Current Rating (Max)                   | 5 A              |
| Contact Retention Within Housing               | Without          |
| Contact Type                                   | Pin              |
| PCB Contact Termination Area Plating Material  | Tin              |
| Contact Mating Area Plating Material           | Gold             |
| Contact Mating Area Plating Material Thickness | .38 µm[15 µin]   |
| Contact Termination Area Plating Thickness     | 2.54 µm[100 µin] |

Termination Features

|                                             |                       |
|---------------------------------------------|-----------------------|
| Termination Post & Tail Length              | 3.18 mm[.125 in]      |
| Termination Method to Printed Circuit Board | Through Hole - Solder |

Mechanical Attachment

|                          |              |
|--------------------------|--------------|
| Strain Relief            | Without      |
| Mating Alignment Type    | Polarization |
| Mating Alignment         | With         |
| Panel Mount Feature      | Without      |
| PCB Mount Retention      | With         |
| PCB Mount Retention Type | Boardlock    |
| Connector Mounting Type  | Board Mount  |
| Mating Retention         | With         |
| Mating Retention Type    | Locking Tab  |

Housing Features

|                    |                        |
|--------------------|------------------------|
| Centerline (Pitch) | 3 mm[.118 in]          |
| Housing Color      | Black                  |
| Housing Material   | High Temperature Nylon |
| Boardlock Material | Nylon                  |

Dimensions

|                             |                  |
|-----------------------------|------------------|
| Row-to-Row Spacing          | 3 mm[.118 in]    |
| PCB Thickness (Recommended) | 1.57 mm[.062 in] |
| Length                      | 6.86 mm          |

Usage Conditions

|  |  |
|--|--|
|  |  |
|--|--|



|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |       |
|---------------------|-------|
| Circuit Application | Power |
|---------------------|-------|

Industry Standards

|                           |                                                      |
|---------------------------|------------------------------------------------------|
| CSA Rating                | Certified                                            |
| Glow Wire Material Rating | Material with GWFI 850°C, Material with GWIT ≥ 775°C |
| UL Flammability Rating    | UL 94V-0                                             |
| Glow Wire Rating          | GWT 750°C (Without Flame)                            |
| Agency/Standard Number    | E28476, VDE_40005280                                 |
| Agency/Standard           | CNR, USR, VDE                                        |
| UL Rating                 | Recognized                                           |
| CSA File Number           | LR7189                                               |
| VDE Tested                | Yes                                                  |

Packaging Features

|                    |                  |
|--------------------|------------------|
| Packaging Method   | Box & Tray, Tray |
| Packaging Quantity | 377              |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 794617-4  
4POS,MICRO MNL,RCPT HSG

Also in the Series | Micro MATE-N-LOK

Insertion & Extraction Tools(1)

Power Contacts(26)

Rectangular Power Connectors(712)

Documents

Product Drawings  
04P MICRO MNL ASSY,R/A,HDR LF  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_3-794619-4\_H.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_3-794619-4\_H.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_3-794619-4\_H.3d\_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_AND\\_SOCKET\\_CONNECTORS\\_CATALOG](#)

English

[MICRO MATE-N-LOK CONNECTOR SYSTEM](#)

English

[1773458-4\\_MICRO\\_MATE\\_N\\_LOK\\_CONNECTOR\\_SYSTEM\\_ORG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD\\_3-794619-4\\_121920171257\\_dmtec](#)

English

[MD\\_3-794619-4\\_121920171257\\_dmtec](#)

English

Agency Approvals

[VDE Certificate](#)

English