



**HOLTITE**

TE Internal #: 4-1437514-7

Pin Sockets, Socket Length 3.45 mm [.136 in], PCB Hole Diameter .064 in [1.61 mm], Open Bottom, .081 – .162 mm<sup>2</sup> Wire Size, 28 – 25 AWG Wire Size

[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets



Socket Length: **3.45 mm [ .136 in ]**

PCB Hole Diameter: **1.61 mm [ .064 in ]**

Socket Sleeve Style: **Open Bottom**

Wire Size: **.081 – .162 mm<sup>2</sup>**

**Features**

**Product Type Features**

Socket Sleeve Style	Open Bottom
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

**Body Features**

Sleeve Material	Copper
Sleeve Plating Material	Tin

**Contact Features**

Contact Spring Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 μm
Contact Mating Area Plating Material	Tin
Contact Base Material	Beryllium Copper
Contact Current Rating (Max)	5 A

**Termination Features**

Insertion Method	Hand/Semi-Automatic/Automatic
Termination Method to Printed Circuit Board	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder



### Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.03 – .05 in]
Socket Length	3.45 mm [.136 in]
PCB Hole Diameter	1.61 mm [.064 in]
Wire Size	.081 – .162 mm <sup>2</sup>
Mating Pin Diameter Range	.64 – .89 mm [.025 – .035 in]

### Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Solder Process Feature	None
Circuit Application	Signal

### Packaging Features

Packaging Quantity	2500
Packaging Method	Reel

### Other

Spring Material	Beryllium Copper
-----------------	------------------

## Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Pb (.6% in Component) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

### Product Drawings

[322-HCS8P3-100=HOLT CNT SKT RE](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437514-7\\_99.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437514-7\\_99.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437514-7\\_99.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Application Specification](#)

English