




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **60**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Unshrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	60
Number of Rows	2
Board-to-Board Configuration	Parallel

Electrical Characteristics

Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 Vrms

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
------------------------------	-----------------



Contact Shape & Form	Square
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold Flash
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Type	Pin
Contact Current Rating (Max)	3 A

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Post & Tail Length	3.18 mm[.125 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	Thermoplastic

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
PCB Thickness (Recommended)	1.4 mm[.055 in]

Usage Conditions

Housing Temperature Rating	Standard
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	CSA LR7189, UL E28476



UL Flammability Rating

UL 94V-0

Packaging Features

Packaging Quantity	50
Packaging Type	Carton

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5-87456-2 60 MODIV HSG DR MRKD .100CL	 TE Part # 3-535512-0 60 MODII HORZ DR CE EESS .100	 TE Part # 5-87456-1 60 MODIV HSG COMP DR .100CL	 TE Part # 173281-2 TOW-PIECE MOD-2 CONN ASSY 70P
--	---	--	---



TE Part # 2-5147722-9
60 MODII HORZ DR SFMNT 30AU



TE Part # 2-535598-2
60 MODIV VRT DR CE RPCT ASSY



TE Part # 3-5535512-0
60 MODII HORZ DR CE EESS .100



TE Part # 5-147721-9
60 MODII HORZ SR SFMNT 30AU



TE Part # 7-535598-2
60 MODIV VRT DR CE RPCT ASSY



TE Part # 8-147102-0
60 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-1
62 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-2
64 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-3
66 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-4
68 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-5
70 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-6
72 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-7
74 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-8
76 MODIV VRT DR 100/SFMNT 30AU



TE Part # 8-147102-9
78 MODIV VRT DR 100/SFMNT 30AU



TE Part # 5-5147721-9
60 MODII HORZ SR SFMNT 30AU

Also in the Series | AMPMODU Headers



PCB Connector Mounting(1)



PCB Connector Shrouds(1)



PCB Headers & Receptacles(6830)



PCB Latches, Locks & Retainers(2)



Wire-to-Board Connector Assemblies & Housings(5)



Wire-to-Board Connector Contacts(66)

Documents

Product Drawings

60 MODII HDR DRST UNSHRD .100

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-87215-0_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-87215-0_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-87215-0_L.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_3-87215-0_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_3-87215-0_J.3d_igs.zip

English

Customer View Model

ENG_CVM_3-87215-0_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5

English

Product Environmental Compliance

TE Material Declaration

3-87215-0

PCB Mount Header, Vertical, Board-to-Board, 60 Position, 2.54 mm [.1 in] Centerline, Unshrouded, Gold, Through Hole - Solder, Signal, AMPMODU Headers



English