

4-160968-2 ✓ ACTIVE

AMP-TY


TE Internal #: 4-160968-2

Cable Ties, Standard, Bag, 82 Newton Tensile Strength, 18.5 lbf Tensile Strength, Product Length 5.27 in [134 mm], Product Width .102 in [2.6 mm]

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Packaging Method: **Bag**

Tensile Strength: **82 Newton**

Product Length: **134 mm [5.27 in]**

Features

Product Type Features

Product Type	Cable Tie
Cable Tie Style	Standard
Tensile Strength	82 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Bundle Range Diameter	32 mm[1.26 in]
Product Length	134 mm[5.27 in]
Product Width	2.6 mm[.102 in]
Product Thickness	1 mm[.039 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-T3437-H85999
High Temperature Markers, HTCM-SCE-TP



TE Part # CAT-T3437-C6298
CM-SCE-TP Military Grade Markers



TE Part # CAT-T3437-K1
K-Type Tie-On Markers



TE Part # CAT-T3437-Z1
Z-Type Push-On Markers



TE Part # 7175170001
CM-SCE-1/2-4H-4



TE Part # 6622650001
CM-SCE-1/2-6H-4



TE Part # 0076930001
CM-SCE-1/2-4H-9



TE Part # 0325090001
CM-SCE-1/2-6H-9



TE Part # 9305490001
HTCM-SCE-1/2-4H-4



TE Part # 0479490001
HTCM-SCE-1/2-4H-9



TE Part # EJ0826-000
CM-SCE-TP-1/4-4H-6



TE Part # EL8598-000
CM-SCE-TP-1/2-6H-3



TE Part # EL8599-000
CM-SCE-TP-1/2-6H-1



TE Part # EL8600-000
CM-SCE-TP-1/2-6H-5



TE Part # A81411-000
HTCM-SCE-TP-1/2-6H-4



TE Part # 6101810001
CM-SCE-1/4-4H-4



TE Part # 6485470001
CM-SCE-1/4-4H-9



TE Part # EC4942-000
11310000



TE Part # EC4943-000
11320000



TE Part # 3576550001
HTCM-SCE-1/4-4H-9

Documents

Product Drawings

[CABLE TY 134X2.6 BLACK](#)

English

Datasheets & Catalog Pages

[CABLE TIES](#)

English